

RTLC incremental linear scale



RTLC 20 or 40 µm linear encoder tape scale combines
±5 µm/m accuracy with the ruggedness of stainless steel. Two versions are available: self-adhesive RTLC-S and RTLC for use with the revolutionary *FASTRACK*™ track system from Renishaw.

Designed for applications that demand high accuracy and an independent expansion coefficient with tape scale convenience, RTLC is read by Renishaw's compact and reliable VIONiC™, TONiC™ and QUANTiC™ readheads.

RTLC-S is laid onto the substrate using its self-adhesive backing tape. An application tool makes this a quick, simple and inexpensive process. A datum clamp is fitted at a single point to lock the scale to the substrate.

RTLC (without self-adhesive) is used with *FASTRACK*. In this case, the scale is held securely in place by two miniature, yet rugged, guide rails. Again, the scale is clamped in a single point to allow independent expansion with extremely low hysteresis, even over wide temperature ranges. If damaged, the scale can be pulled out of the guide rails and quickly replaced, even where access is limited, thus reducing machine downtime. This feature also makes the new linear encoder system ideal for large machines that need to be sectioned for transportation.

- Scale accuracy up to ±5 μm/m.
 Further improvement possible with error correction
- 20 µm and 40 µm pitch versions available
- · 'Cut to length' flexibility
- Compatible with VIONiC, TONiC and QUANTiC high-performance readheads
- RTLC scale expands at its own low thermal coefficient (10.1 ±0.2 μm/m/°C @ 20 °C)
- Use with FASTRACK for very low hysteresis
- FASTRACK guide rails are pre-aligned in reels for cut-to-suit flexibility
- Quick installation. FASTRACK adds fast scale replacement capability
- Scale can be locked to the substrate at a single datum point anywhere along the axis
- RTLC scale can bridge gaps in the FASTRACK up to 25 mm
- High solvent immunity



General specifications

Coefficient of thermal expansion (at 20 °C)	10.1 ±0.2 μm/m/°C
Temperature (system)	Storage -20 °C to +70 °C
	Operating 0 °C to +70 °C
Humidity (system)	95% relative humidity (non-condensing) to IEC 60068-2-78
Shock (system)	Operating 500 m/s ² , 11 ms, ½ sine, 3 axe
Vibration (system)	Operating 100 m/s² max @ 55 to 2000 Hz, 3 axes

RTLC-S scale specifications

Self-adhesive incremental scale

Form (H × W)		0.4 mm × 8 mm including adhesive
Pitch	RTLC20-S	20 μm
	RTLC40-S / RTLC40H-S	40 μm
Accuracy (at 20 °C)	RTLC20-S / RTLC40H-S	±5 μm/m
	RTLC40-S	±15 μm/m
Linearity	RTLC20-S / RTLC40H-S	±2.5 μm/m achievable with two point error correction
	RTLC40-S	$\pm 5~\mu\text{m/m}$ achievable with two point error correction
Maximum supplied length		10 m [†]
Material		Hardened and tempered stainless steel
Mass		12.9 g/m

RTLC scale and FASTRACK carrier specifications

Incremental scale for use with FASTRACK carrier self-adhesive mounting system

Form (H × W)		0.4 mm × 18 mm including adhesive
Pitch	RTLC20	20 μm
	RTLC40 / RTLC40H	40 μm
Accuracy (at 20 °C)	RTLC20 / RTLC40H	±5 μm/m
	RTLC40	±15 μm/m
Linearity	RTLC20 / RTLC40H	±2.5 μm/m achievable with two point error correction
	RTLC40	$\pm 5~\mu\text{m/m}$ achievable with two point error correction
Maximum supplied length RTLC		10 m
	FASTRACK	25 m
Minimum recommended length	of FASTRACK	100 mm
Material RTLC		Hardened and tempered stainless steel
	FASTRACK	Hardened stainless steel
Mass	RTLC	12.2 g/m
	FASTRACK	24 g/m

 $^{^{\}dagger}\textsc{For lengths}$ >2 m FASTRACK with RTLC is recommended.

Reference mark

Туре	IN-TRAC [™] reference mark, directly embedded into incremental track 50 mm (nominal) spacing. Bi-directional position repeatability
Selection	Single reference mark selection by magnetic actuator (A-9653-0143) customer positioned
Repeatability	Unit of resolution repeatability (bi-directional) across full system rated speed and temperature ranges

Limit switches

Туре	Magnetic actuators; with dimple triggers Q limit, without dimple triggers P limit (see RTLC scale installation drawing)
Trigger point	The limit output is nominally asserted when the readhead limit switch sensor passes the limit magnet leading edge, but can trigger up to 3 mm before that edge
Mounting	Customer placed at desired locations
Repeatability	< 0.1 mm



Compatible readheads

	VIONIC	TONIC	QUANTIC
	MADE IN UK CC	o los los los los los los los los los lo	
Scale type	RTLC20	RTLC20	RTLC40
Pitch	20 μm	20 μm	40 μm
Outputs	Digital resolutions from 5 μm to 2.5 nm direct from the readhead	Analogue 1 Vpp. Digital resolutions from 5 μm to 1 nm from an interface.	Analogue 1 Vpp. Digital resolutions from 10 µm to 50 nm direct from the readhead.
SDE (typical)	< ±15 nm	±30 nm	< ±80 nm*
Jitter (RMS)	down to 1.6 nm	down to 0.5 nm	down to 2.73
Maximum speed	12 m/s	10 m/s	24 m/s*

^{*}Digital variants.

Readhead features

- Filtering optics and Auto Gain Control for high reliability and solid Lissajous signals.
- Dynamic signal processing ensures ultra-low sub-divisional error (SDE). Result: smoother scanning performance.
- High signal-to-noise ratio provides ultra-low jitter for optimum positional stability.
- Auto-phasing of *IN-TRAC* reference mark.
- Clocked outputs ensure optimised speed performance for all resolutions, for a wide variety of industry-standard controllers.
- DOP Dual output interfaces available to provide simultaneous analogue and digital outputs (TONiC systems only).




RTLC and FASTRACK carrier installation drawing

(adhesive datum clamp method†)

For further details, please refer to the relevant system installation guides.



Dimensions and tolerances in mm



Assumes 1 mm gap between scale and end covers and zero gap between FASTRACK and end covers. For alternative mechanical datum clamp method refer to the relevant system Installation guide. NOTES: Minimum recommended FASTRACK length = 100 mm. The reference mark selector and limit actuator locations are correct for the readhead orientation shown.




RTLC-S installation drawing

(Adhesive datum clamp method)

For further details, please refer to the relevant system installation guides.



Dimensions and tolerances in mm



† Dimensions from scale surface. NOTE: Bolted reference mark selector and limits also available. See the relevant system installation guide for details.



Scale part numbers

RTLC

Stainless steel tape scale for use with the FASTRACK carrier.

		Distance from		From Part number (where xxxx is the length in cm)*		
Available lengths	Available in increments of	Reference mark spacing	scale end to first reference mark	RTLC20 (Compatible with VIONiC and TONiC)	RTLC40 (Compatible with QUANTiC)	RTLC40H (Compatible with QUANTiC)
20 mm to 100 mm	10 mm	Middle of scale length	Middle of scale length	A-9705-xxxx	A-6566-xxxx	A-6668-xxxx
> 100 mm to 10 m	10 mm	50 mm	50 mm	A-9705-XXX	A-0500-xxxx	A-0000-XXXX

FASTRACK carrier

Stainless steel carrier for use with RTLC tape scale.

Available lengths	Available in increments of	Part number (where xxxx is the length in cm)*
100 mm to 25 m	25 mm [†]	A-9704-xxxx

[†] Part numbers for *FASTRACK* lengths ending in 25 mm are: A-9704-xxx3
Part numbers for *FASTRACK* lengths ending in 75 mm are: A-9704-xxx8

RTLC-S

Stainless steel tape scale with self-adhesive backing tape.

	Dis	Distance from	Part number (where xxxx is the length in cm)*			
Available lengths	Available in increments of	Reference mark spacing	scale end to first reference mark	RTLC20-S (Compatible with VIONiC and TONiC)	RTLC40-S (Compatible with QUANTiC)	RTLC40H-S (Compatible with QUANTiC)
20 mm to 100 mm	10 mm	Middle of scale length	Middle of scale length	A-9715-xxxx	A 6567 mag	A-6670-xxxx
> 100 mm to 10 m	10 mm	50 mm	50 mm	H-9/ 10-XXXX	A-6567-xxxx	A-007U-XXXX

^{*}Ordering A-9705-0070, for example, will result in a length of 70 cm of RTLC20.



Accessory part numbers

Reference mark and limit magnets[†]

Part description	Part number	Product image
Reference mark selector magnet – Adhesive mounted	A-9653-0143	II. II
Bolted reference mark selector magnet (For use with RTLC-S only)	A-9653-0290	
Q limit switch actuator magnet – Adhesive mounted	A-9653-0139	II. II
Bolted Q limit switch actuator magnet (For use with RTLC-S only)	A-9653-0291	
P limit switch actuator magnet – Adhesive mounted	A-9653-0138	
Bolted P limit switch actuator magnet (For use with RTLC-S only)	A-9653-0292	
Magnet applicator device (Aids positioning)	A-9653-0201	

 $^{^\}dagger Longer\ limit\ magnets\ are\ available.\ Contact\ your\ local\ Renishaw\ representative\ for\ more\ information.$

Datum clamps

Part description	Part number	Product image
Self-adhesive datum clamp (For use with RTLC-S only)	A-9585-0028	
Loctite 435 adhesive – 20 g bottle (For securing axis datum position of RTLC in FASTRACK carrier or RTLC-S)	P-AD03-0012	LOCTITE. MINANT ADMESTOR SOFOTT MEESTOR
Dispensing tip for Loctite 435 adhesive	P-TL50-0209	
Bolted datum clamp (For use with RTLC and <i>FASTRACK</i> only)	A-9589-0077	



Accessory part numbers (continued)


RTLC/RTLC-S scale and FASTRACK accessories

Part description	Part number	Product image
Guillotine (For cutting RTLC/RTLC-S scale and <i>FASTRACK</i> carrier)	A-9589-0071	
Shears (For cutting RTLC/RTLC-S scale and FASTRACK carrier)	A-9589-0133	
RTLC-S scale applicator	A-9589-0115	
FASTRACK centre section removal tool (Removes centre section of FASTRACK when carrier has been mounted)	A-9589-0066	
FASTRACK separator assembly (Removes centre section of FASTRACK when carrier has been mounted – includes removable side panels for use when FASTRACK is mounted against a ledge or dowels)	A-9589-0122	
RTLC scale pulling tool (Aids installation of RTLC scale through the FASTRACK carrier)	A-9589-0420	ALERO CASO
End cover kit (RTLC-S only)	A-9585-0035	REVISIOUVEI ERSVISIOUVEI ERSVISIOUVEI ERIVISIOEVEI
End cover kit (<i>FASTRACK</i> only)	A-9589-0058	

www.renishaw.com



Compatible products



For worldwide contact details, visit www.renishaw.com/contact

© 2009–2020 Renishaw plc. All rights reserved.

RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries.

Loctite® is a registered trade mark of the Henkel Corporation.

Other brand, product or company names are trade marks of their respective owners.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. RENISHAW RESERVES THE RIGHT TO MAKE CHANGES TO THIS DOCUMENT AND TO THE EQUIPMENT, AND/OR SOFTWARE AND THE SPECIFICATION DESCRIBED HEREIN WITHOUT OBLIGATION TO PROVIDE NOTICE OF SUCH CHANGES.



Part no.: L-9517-9417-06-B Issued: 12.2020